

## QSiI PLE Cure Rate Modifier for Platinum Catalyzed Silicone Materials

### Description

QSiI PLE can be used with two-component, room temperature, addition cure silicone materials to increase the work life of the elastomer system. The final cure time may also be significantly increased.

Note: QSiI PLE is not recommended to be used with the following products: QM 226, QM 230, QM 232, QM 230F, QM 237, QM 245, QM 247, QM 255 and Stretch FX.

### Key Features

- Ease of use
- Increases work life
- Can be used with platinum (addition) cure silicone elastomers

### Use and Cure Information

#### CURE CHARACTERISTICS

It is highly recommended that a test batch be run before scaling up to larger quantities. Each silicone elastomer has unique curing profiles and most likely will require differing amounts of QSiI PLE to get to the desired pot-life. A good starting point is as follows:

RATIO BY WEIGHT*			
Mix Ratio of System	A component	B component	QSiI PLE
10:1	100	10	0.25
1:1	100	100	0.5

\*Follow elastomer mix ratio instructions and pay special attention to mix ratio directions.

Some elastomers may require mixing by volume.

It is important to note that with most platinum cure systems, the longer work-time will also result in a longer time to total cure. The curing process begins as soon as the catalyst is mixed with the base and QSiI PLE. Under normal temperature (25°C) and humidity (50% RH) conditions, the material will cure as described in the data above. Any large change in temperature (+/-5°C) or humidity (> 60% – 70%) may alter the cure profile of the material. In addition, if the product is to be used in a harsh environment or with aggressive resins such as high styrene polyester resins in moldmaking applications, it is recommended that the rubber be allowed to cure for 48 hours.

For best results, A and B components from the same lot number should be used.

### Health & Safety

Safety Data Sheet available on request.

Revision Date 14 Oct 2021  
Revision No 6  
Download Date 08 May 2024

The content set out in the technical data sheet does not contain information upon which you should rely. It is provided for general information purposes only and does not constitute a product specification. You must obtain professional or specialist advice before taking any action based on the information provided in the technical data sheet. CHT make reasonable efforts to ensure that information set out in the technical data sheet is complete, accurate, and up-to-date. CHT do not, however, make any representations, warranties or guarantees (whether express or implied) that information set out in the technical data sheet is complete, accurate, or up-to-date or that the product will be suitable for your requirements. You should carry out your own testing to determine the applicability of such information and whether the product will be suitable. CHT reserve the right to modify the technical data sheet at any time. The CHT technical service department is available to offer further information and advice and should it be needed to look at modifying current products or custom formulate a new one to meet your specific requirements. Please contact the technical service department.

CHT Germany GmbH: Postfach 12 80, 72002 Tübingen, Bismarckstraße 102, 72072 Tübingen, Germany  
Telephone: 07071/154-0, Fax: 07071/154-290, Email: info@cht.com, Homepage: www.cht.com / www.cht-silicones.com